



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR1000U ****Delisted*** 1000W BT56 Metal Halide Clear Mog Base

Ge By Current Lamps

Catalog Number	MVR1000U
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 100280 LM (Horizontal);108000 LM (Vertical) Brightness (Lumens), 1000 W, Clear, Hard Glass Material, 11000 H (Horizontal);15000 H (Vertical) Average Life, Mogul Base, M47 Ansi Ballast Code, Non Dimmable, 7 In Diameter, 15.37 In Height, 150 % Mercury Content, 8.01 LB
Weight per unit	1.2 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
------	-------------------

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Style	Open Fixture-Restricted Position (S-Rated)

Descriptions

Description	**DELISTED* 1000W BT56 METAL HALIDE CLEAR MOG BASE
Special Features	15.37IN Length

Manufacturer Information

Brand	GE Current
GTIN	00043168418263
UPC	043168418263

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	6
Weight Per each	1.23

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------