



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR100UMED 100W BD17 Metal Halide Clear Medium Base Lamp

Ge By Current Lamps

| | |
|------------------|---|
| Catalog Number | MVR100UMED |
| Manufacturer | Ge By Current Lamps |
| Description | Metal Halide Lamp, 70, 4000 K, 9500 LM Brightness (Lumens), 100 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M90 Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Height, 8.5 % Mercury Content, 2.0 LB |
| Weight per unit | 0.3300 (lbs/each) |
| Product Category | Hid Quartz Metal Halide Lamps |

Features

| | |
|----------------|--------------------|
| Base | Medium Screw (E26) |
| lumens | 9500 |
| Voltage Rating | 100 |
| Wattage | 100 |

Material, Color, and Finish

| | |
|-----------------------------|------------------------|
| Color | Clear |
| color rendering index (cri) | 70 |
| Finish | Clear |
| Style | Enclosed fixtures only |

Descriptions

| | |
|------------------------|---|
| Description | 100W BD17 METAL HALIDE CLEAR MEDIUM BASE LAMP |
| extra long description | GEL MVR100/U/MED 12652 MULTIVAPOR |
| Special Features | 5.43IN Length |

Manufacturer Information

| | |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168126526 |
| UPC | 043168126526 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.33 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|