



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1915 Turning Basin Suite 500
77029-0000, TX Houston
Phone: 713-675-6700
Fax: 713-675-6777



MVR175U 175W ED28 Metal Halide Clear Mogul Base Lamp

Ge By Current Lamps

Catalog Number	MVR175U
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 11700 LM (Horizontal);13600 LM (Vertical) Brightness (Lumens), 175 W, Clear, Hard Glass Material, 6000 H (Horizontal);10000 H (Vertical) Average Life, Mogul Base, M57 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 25.74 % Mercury Content, 5.24 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
Wattage	175

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Style	Enclosed fixtures only

Descriptions

Description	175W ED28 METAL HALIDE CLEAR MOGUL BASE LAMP
extra long description	GEL MVR175/U 47760 MULTIVAPOR
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168477604
UPC	043168477604

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	12
Weight Per each	0.46