



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR250VBUPA \*Delisted\* 250W PS/MH Mog Vert Base Up Burn Pos

Ge By Current Lamps

Catalog Number	MVR250VBUPA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4200 K, 23000 LM Brightness (Lumens), 250 W, Clear, Hard Glass Material, 15000 H Average Life, Mogul Base, M138/M153 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 27 % Mercury Content, 5.37 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (E39)
lumens	23000
Wattage	250

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Enclosed fixtures only

### Descriptions

Description	*DELISTED* 250W PS/MH MOG VERT BASE UP BURN POS
extra long description	GEL MVR250/VBU/PA 26317 MULTIVAPOR
Special Features	8.25IN Length

### Manufacturer Information

Brand	GE Current
GTIN	00043168263177
UPC	043168263177

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	12
Weight Per each	0.46

### Uses, Certifications, and Standards

Application	Vertical base up +/-15°
-------------	-------------------------