



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR400H0RED28PA MH Lamp

Ge By Current Lamps

| | |
|------------------|---|
| Catalog Number | MVR400H0RED28PA |
| Manufacturer | Ge By Current Lamps |
| Description | Metal Halide Lamp, 65, 4100 K, 38000 LM Brightness (Lumens), 400 W, Clear, Hard Glass Material, 20000 H Average Life, E39 Mogul Screw Base, M135/M155 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 40 % Mercury Content, 5.91 LB |
| Weight per unit | 0.4600 (lbs/each) |
| Product Category | Hid Quartz Metal Halide Lamps |

Features

| | |
|---------|-------------------|
| Base | Mogul Screw (E39) |
| lumens | 38000.0 |
| Wattage | 400.0 |

Material, Color, and Finish

| | |
|-----------------------------|------------------------|
| Color | Clear |
| color rendering index (cri) | 65.0 |
| Finish | Clear |
| Style | Enclosed fixtures only |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | MH LAMP |
| extra long description | GEL MVR400HOR/ED28PA 72885 MULTIVAP |
| Special Features | 8.25IN Length |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168728850 |
| Manufacturers Part Number | MVR400HOR/ED28PA |
| UPC | 043168728850 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.46 |

Uses, Certifications, and Standards

| | |
|-------------|-------------------|
| Application | Horizontal +/-75° |
|-------------|-------------------|