

CONNECTORS

Split Bolt Connectors

Copper Split Bolts 2 Wire

N Series



SPECIFICATIONS

- UL486A Listed Wire Connector.
- UL486D Listed Direct Bury.

FEATURES

- High strength solderless service connector made of high-copper alloy for copper and copperweld wires.
- Type for two maximum wire sizes.

CAT. NO.	COPPER CONDUCTOR			MAXIMUM CONDUCTOR COPPERWELD		WIRE DIA. RANGE IN.	REC. TORQUE (IN. LB.)	STD. CTN. QTY.
	RANGE OF EQUAL MAIN & TAP		MIN. TAP WITH ONE MAX. MAIN	STR	TYPE A			
	MIN.	MAX.						
N-10	16 STR	10 STR	16 STR	–	–	0.057 – 0.116	80	100
N-8	16 STR	8 STR	16 STR	–	–	0.057 – 0.145	80	100
N-6	10 SOL	6 SOL	16 SOL	–	–	0.102 – 0.162	165	100
N-4	8 SOL	4 SOL	16 SOL	3 NO.12	8A	0.128 – 0.204	165	75
N-3	6 SOL	2 SOL	16 SOL	3 NO. 9	5A	0.162 – 0.258	275	50
N-2	6 SOL	2 STR	14 STR	3 NO. 7	3A	0.162 – 0.292	275	40
N-1/0	4 SOL	1/0 STR	14 SOL	3 NO. 6	2A	0.204 – 0.375	385	20
N-2/0	2 SOL	2/0 STR	14 STR	3 NO. 5	–	0.258 – 0.418	385	15
N-3/0	2 SOL	3/0 STR	12 SOL	7 NO. 7	–	0.258 – 0.470	500	10
N-250	1/0 SOL	250 MCM	10 SOL	7 NO. 5	–	0.325 – 0.575	650	6
N-350	4/0 STR	350 MCM	8 SOL	19 NO. 7	–	0.528 – 0.682	650	4
N-500	250 MCM	500 MCM	8 SOL	19 NO. 6	–	0.575 – 0.815	825	3
N-750	350 MCM	750 MCM	8 SOL	19 NO. 5	–	0.682 – 0.999	1000	2
N-1000	500 MCM	1000 MCM	8 SOL	–	–	0.815 – 1.153	1100	2