


All Purpose Type Split Bolts - N-250SP



Drawn - SD

Approved - KM

Material - Copper / Finish: Tin Plated

Title - All Purpose Type Split Bolts



Max Run To Max Tap	250 - 250 STR AL-CU
Min Run To Min Tap	4/0 - 8 STR AL-CU
Max Run To Min Tap	250 - 8 STR AL-CU
Min Equal Run - Tap	1 - 1 STR AL-CU
4	Spacer Electrolytical Copper
3	Nut Bronze
2	Rider Bronze
1	Body Electrolytical Copper

