



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **N3 #3 Cu Split Bolt** *Nsi Industries*

Catalog Number	N3
Manufacturer	Nsi Industries
Description	Copper Split Bolt Connector 3 Awg Copper Split Bolt Connectors Are High-Strength Solderless Service Connectors Made Of High-Copper Alloy For Copper and Copperweld Wires. Type For Two Maximum Wire Sizes.
Weight per unit	0.1000 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	6 SOL - 2 SOL
Wire Type	Class A & B

### **Material, Color, and Finish**

Color	Copper
Finish	COPPER

### **Dimensions and Weight**

Size	L=1.153 - W=.748
------	------------------

### **Descriptions**

Description	#3 CU SPLIT BOLT
extra long description	NSI N-3 Split Bolt Copper 3
Features	Copper Split Bolt Connector 3 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.
Long Description	Copper Split Bolt Connector 3 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.
Product Type	Split Bolt Copper 3
Special Features	6 SOL-2 SOL - 50 Pack

### **Manufacturer Information**

Brand	NSi
GTIN	00662381020048
UPC	662381020048



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description.....SPLIT BOLTS

Type.....Copper Split Bolts

## Packaging

Carton.....1

Package.....50

Weight Per each.....0.1

## Uses, Certifications, and Standards

Application.....Wire Termination

environmental conditions.....90 C

standard.....UL486B

Temperature Rating.....90 C