


Copper Split Bolts - N-3

Drawn - SD		
Approved - KM		
Material - Copper		
Title - Copper Split Bolts		
		
Max Run To Max Tap	2 - 2 STR	
Min Run To Min Tap	6 - 16 STR	
Max Run To Min Tap	2 - 16 STR	
Min Equal Run - Tap	6 - 6 STR	
3	Nut	Bronze
2	Rider	Bronze
1	Body	Electrolytical Copper



NOTE: 1- TORQUE TO BE APPLIED: 3.17 kgf.m
 2- PULL-OUT: 81.65 kgf
 3- Dimensions in mm.