



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82  
76240-0000, TX Gainesville  
Phone: 940-612-1388  
Fax: 940-612-1499



## **N6 #6 Cu Split Bolt** *Nsi Industries*

Catalog Number	N6
Manufacturer	Nsi Industries
Description	Split Bolt Connector, #10 Awg (Range Of Equal Main and Tap-Solid) Conductor Size, #6 Awg (Range Of Equal Main and Tap-Stranded);#16 Awg (Minimum Tap With One Maximum Main-Stranded) Conductor Size, Non-Insulated, Copper;Copperweld Conductor Material, 2 Conductors, +90 °C Operating Temperature, 0.866 In Overall Length, Split Terminal, 600 V, 0.055 LB/Ea
Weight per unit	0.0550 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	10 SOL - 6 SOL
Wire Type	Class A & B

### **Material, Color, and Finish**

Color	Copper
Finish	COPPER
Housing Material	Copper

### **Dimensions and Weight**

Size	L=.866 - W=.492
------	-----------------

### **Descriptions**

Description	#6 CU SPLIT BOLT
extra long description	NSI N-6 Split Bolt Copper 6
Features	Copper Split Bolt Connector 6 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.

### **Manufacturer Information**

GTIN	00662381020024
UPC	662381020024

### **Taxonomies, Classifications, and Categories**

Category Description	SPLIT BOLTS
Type	Copper Split Bolts



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82  
76240-0000, TX Gainesville  
Phone: 940-612-1388  
Fax: 940-612-1499

## Packaging

Carton	1
Package	100
Weight Per each	0.055

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B