

Non-Metallic Push-In Connector

Made in USA 

NEW!
more on
reverse

For NM and Flexible Cord Installations in New Work and Retrofit



**For installation in
an INSTALLED box**




...or in NEW work

Arlington's **NMR840** offers easy, push-in installation in a new box, or an installed box in an existing wall.

NMR840 installs from *INSIDE* the box – or from *OUTSIDE* the box.

Installation is easy *and secure!*

Once inserted into the connector slot and locked down, the wedge holds cable securely in place...no pullout!



- 3/8" trade size fits 1/2" knockout
- For NM and flexible cord:
 - (1) 14/2 flat to (1) 10/3 round cables
 - (2) 14/2 to (2) 12/2 flat cables
 - (1) 14/3 to (1) 10/3 flat cable
 - (2) 14/3 to (2) 12/3 flat cable
 - (1) 14/3 to (1) 10/3 round cable
- Cord ranges .350" to .490"
- c UL us Listed



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Non-Metallic Push-In Connectors


NEW!

NMR840 for New Work or Retrofit

NMR840: Easy installation in Installed Box...




Feed cable through the knockout, then into the connector.



Insert wedge in slot in connector. Lock tight with pliers.



Push assembly into box...




Done!

...or New Work




Feed cable into connector.



Insert wedge into slot in connector. Lock tight with pliers.



Push assembly through knockout...



...and push into box. Done!

NMR840

NEW!

Patent pending



NM840

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade size	KO Size	Unit Pkg	Std Pkg
----------------	---------------------------	------------	---------	----------	---------

NMR840	14940	3/8	1/2	100	1000
---------------	-------	-----	-----	-----	------

Push in, non-metallic connector for installation of NM cable or flexible cord ranges: .350" to .490" in new work or an installed box in an existing wall (See cable ranges on front)

Also Available for New Work

Visit website for complete cable ranges

NM840	54840	3/8	1/2	100	1000
NM841	54841	1/2	1/2	50	500
NM842	54842	3/4	3/4	25	250
NM843	54843	1	1	25	250
NM844	50175	1-1/4	1-1/4	10	100



NM841

Distributed by



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Made in USA

Non-Metallic Push-In Connector

Made in USA 

NEW!
more on
reverse


For NM and Flexible Cord Installations in New Work and Retrofit



NMR840
Non-metallic
push in connector

Patent pending

**For installation in
an INSTALLED box**



New work

...or in NEW work

- 3/8" trade size fits 1/2" knockout
- For NM and flexible cord:
 - (1) 14/2 flat to (1) 10/3 round cables
 - (2) 14/2 to (2) 12/2 flat cables
 - (1) 14/3 to (1) 10/3 flat cable
 - (2) 14/3 to (2) 12/3 flat cable
 - (1) 14/3 to (1) 10/3 round cable
- Cord ranges .350" to .490"
- c UL us Listed



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Non-Metallic Push-In Connectors


NEW!

NMR840 for New Work or Retrofit

NMR840: Easy installation in Installed Box...




Feed cable through the knockout, then into the connector.



Insert wedge in slot in connector. Lock tight with pliers.



Push assembly into box...




Done!

...or New Work




Feed cable into connector.



Insert wedge into slot in connector. Lock tight with pliers.



Push assembly through knockout...



...and push into box. Done!

NMR840

NEW!

Patent pending



NM840

Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade size	KO Size	Unit Pkg	Std Pkg
----------------	---------------------------	------------	---------	----------	---------

NMR840	14940	3/8	1/2	100	1000
---------------	-------	-----	-----	-----	------

Push in, non-metallic connector for installation of NM cable or flexible cord ranges: .350" to .490" in new work or an installed box in an existing wall (See cable ranges on front)

Also Available for New Work

Visit website for complete cable ranges

NM840	54840	3/8	1/2	100	1000
NM841	54841	1/2	1/2	50	500
NM842	54842	3/4	3/4	25	250
NM843	54843	1	1	25	250
NM844	50175	1-1/4	1-1/4	10	100



NM841

Distributed by



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Made in USA