

MORE
on
reverse

Black Button™ NM Cable connectors

Non-metallic • Easy, push-in installation



Reduce labor costs with Arlington's **Black Button™** NM cable connectors. They are the lowest cost NM cable connectors on the market, and offer the fastest installation. Simply push the connector into the knockout. That's it.

Listed for single or multiple cables, Arlington's Black Button connectors offer smooth, easy cable insertion while exceeding UL and CSA pullout requirements.

They are removable and reusable too.




1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description	KO Size	Unit Pkg	Std Pkg
NM94	05488	3/8 Black Button NM Cable connectors	1/2	250	1000
NM940	72156	3/8 Black Button NM Cable connectors	1/2	100	1000
NM95	10956	3/4 Black Button NM Cable connectors	3/4	50	500
NM96	72158	1 Black Button NM Cable connectors	1	25	250

Patent pending

Black Button™ NM Cable connectors

Non-metallic • Easy, push-in installation



- Listed for one or two cables
- Easy installation
- Smooth, easy cable insertion
- Secure hold on cable – exceeds UL pullout tests



1 Push the NM cable connector into the knockout with light finger pressure.



2 Install one or two cables, fast! Push the NM cable (or cables) into the connector to the desired length.

For multiple cable installations:

- Two cables may be inserted together or individually.
- A second cable may be added without removing the first.

Cable Ranges:

NM94	One 6/2 - 14/2
	One 12/4
	Two 10/2 - 14/2
	One 10/3 - 14/3
	One 10/2 and One 14/2
	One 12/2 and One 14/2
	One 10/2 and One 12/2
	Two 14/3
	Two 12/3
NM95	One 6/2 - 14/2
	One 6/3 - 14/3
	One 12/4
	Two 10/2 - Two 14/2
	Two 10/3 - Two 14/3
	One 14/2 - One 12/2
	One 14/2 - One 10/2
NM96	One 4/3 - 8/3
	One 6/2 - 6/3



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Distributed by

MORE
on
reverse

Black Button™ NM Cable connectors

Non-metallic • Easy, push-in installation



Reduce labor costs with Arlington's **Black Button™** NM cable connectors. They are the lowest cost NM cable connectors on the market, and offer the fastest installation. Simply push the connector into the knockout. That's it.

Listed for single or multiple cables, Arlington's Black Button connectors offer smooth, easy cable insertion while exceeding UL and CSA pullout requirements.

They are removable and reusable too.




1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description	KO Size	Unit Pkg	Std Pkg
NM94	05488	3/8 Black Button NM Cable connectors	1/2	250	1000
NM940	72156	3/8 Black Button NM Cable connectors	1/2	100	1000
NM95	10956	3/4 Black Button NM Cable connectors	3/4	50	500
NM96	72158	1 Black Button NM Cable connectors	1	25	250

Patent pending

Black Button™ NM Cable connectors

Non-metallic • Easy, push-in installation



- Listed for one or two cables
- Easy installation
- Smooth, easy cable insertion
- Secure hold on cable – exceeds UL pullout tests



1 Push the NM cable connector into the knockout with light finger pressure.



2 Install one or two cables, fast! Push the NM cable (or cables) into the connector to the desired length.

For multiple cable installations:

- Two cables may be inserted together or individually.
- A second cable may be added without removing the first.

Cable Ranges:

NM94	One 6/2 - 14/2
	One 12/4
	Two 10/2 - 14/2
	One 10/3 - 14/3
	One 10/2 and One 14/2
	One 12/2 and One 14/2
	One 10/2 and One 12/2
	Two 14/3
	Two 12/3
NM95	One 6/2 - 14/2
	One 6/3 - 14/3
	One 12/4
	Two 10/2 - Two 14/2
	Two 10/3 - Two 14/3
	One 14/2 - One 12/2
	One 14/2 - One 10/2
NM96	One 4/3 - 8/3
	One 6/2 - 6/3



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Distributed by