

A Arlington

Part : NMLT90125

Description: 90° Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.320 lbs/each

Height: 4.650"

Width: 4.440"

Additional Color Options:  <http://www.aifittings.com/catalog/images/colors/black.png> height="16" width="16"

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1-1/4"

Trade Size: 1-1/4"

Packaging

Unit: 5 pcs

Standard: 25 pcs



A Arlington

Part : NMLT90125

Description: 90° Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.320 lbs/each

Height: 4.650"

Width: 4.440"

Additional Color Options:  <http://www.aifittings.com/catalog/images/colors/black.png> height="16" width="16"

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1-1/4"

Trade Size: 1-1/4"

Packaging

Unit: 5 pcs

Standard: 25 pcs

