



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NTCC100 1" Rigid Threadless Raintight Coupling *Appleton/Oz Gedney*

Catalog Number	NTCC100
Manufacturer	Appleton/Oz Gedney
Description	Coupling, Trade Size: 1 In, Outside Diameter: 1.88 In, Length: 2-1/2 In, Flexibility: Rigid and Imc, Material: Steel and Malleable Iron, Connection: Compression, Standard: UI 514B, UI File Number E11853, Nema FB-1, For Joining Lengths Of Steel Emt to Rigid Metal Conduit or Imc
Weight per unit	0.5700 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Compression
outside diameter	1.8800000000000000;47.7520

### Dimensions and Weight

Length	2-1/2
--------	-------

### Descriptions

Description	1" RIGID THREADLESS RAIN TIGHT COUPLING
extra long description	APP NTCC-100 1 IN CPLG NO THRD RGD
Long Description	Coupling, Trade Size: 1 IN, Outside Diameter: 1.88 IN, Length: 2-1/2 IN, Flexibility: Rigid And IMC, Material: Steel And Malleable Iron, Connection: Compression, Standard: UL 514B, UL File Number E11853, NEMA FB-1, For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
Product Type	1 In CPLG No THRD RGD Cond
Special Features	Threadless, Concretetight

### Manufacturer Information

Brand	Appleton
GTIN	00781381638302
Manufacturers Part Number	NTCC-100
UPC	781381638302

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	COUPLING

### Trade Size

Trade Size	1
------------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 25

Weight Per each ..... 0.57

## Uses, Certifications, and Standards

Application ..... For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC

standard ..... UL 514B, UL File Number E11853, NEMA FB-1