



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NTL873NICC6 Radiant Night Light + SP/3WAY Switch Ni

Pass & Seymour/Legrand

Catalog Number	NTL873NICC6
Manufacturer	Pass & Seymour/Legrand
Description	15A 120V Single Pole/3-Way Switch With Led Night Light, Nickel Finish
Weight per unit	0.3000 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	120
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Poles	Single Pole, 3-Way
Switch Type	Push
Voltage	120.0 V
Voltage Rating	120

Material, Color, and Finish

Color	Nickel
-------	--------

Dimensions and Weight

Size	Depth 1.5" x Width 1.6" x Height 2.75"
------	--

Descriptions

Description	RADIANT NIGHT LIGHT + SP/3WAY SWITCH NI
extra long description	P&S NTL873NICC6 RADIANT NIGHT LIGHT
Features	Nightlight
Long Description	15A 120V Single Pole/3-Way Switch with LED Night Light, Nickel Finish
Product Type	Radiant Night Light + SP/3WAY Switch Ni
Special Features	This night light replaces any existing single-pole or 3-way switch devices and offers a hidden sensor that automatically controls the night light, plus five adjustable light levels (including OFF).



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007032352
Manufacturers Part Number	NTL873NICC6
UPC	785007032352

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Nightlight

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	6
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	UL, CULUS, cULus, UL Listed