



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P200351B 22/4C STR BC NS TWSTR CMP/CL3P *Southwire Company*

| | |
|------------------|--|
| Catalog Number | P200351B |
| Manufacturer | Southwire Company |
| Description | 22 Awg 4/C Stranded Unshielded CMP/CL3P/FPLP Cable |
| Weight per unit | 15.0 (lbs/ft) |
| Product Category | 20190712103432 |

Features

| | |
|----------------------|------------|
| amperage rating | CL3 |
| Conductor Size | 22 |
| core | UNSHIELDED |
| Number of Conductors | 4 |
| outside diameter | 0.146 |
| Resistance | 17.5 |
| strands | 7 |
| Voltage Rating | 300 |

Material, Color, and Finish

| | |
|---------------------|--------|
| Color | White |
| Conductor Material | BC |
| Finish | BULK |
| Insulation Material | LS-PVC |
| Jacket Material | LS-PVC |

Dimensions and Weight

| | |
|--------|------|
| Length | 1000 |
|--------|------|

Descriptions

| | |
|------------------------|--|
| Construction | CABLE |
| Description | 22/4C STR BC NS TWSTR CMP/CL3P |
| extra long description | SWC P20035-1B 22 AWG 4/C STRANDED U |
| Long Description | 22 AWG 4/C STRANDED UNSHIELDED CMP/CL3P/FPLP CABLE |
| Product Type | 22 Awg 4/C Stranded Unshielded CMP/CL3P/FPLP Cable |
| Special Features | CL3P |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Cables & Cords |
| GTIN | 00032886881633 |
| Manufacturers Part Number | P20035-1B |
| UPC | 032886881633 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type | CMP |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight | 15 |
| Weight Per foot | 15 |

Uses, Certifications, and Standards

| | |
|--------------------|--------|
| Application | CL3 |
| standard | UL 444 |
| Temperature Rating | 75 |