

# P2612 Fan Light Kit

• Dry location listed 

## Description:

Alabaster style glass bowl ceiling fan light kit casts an inviting illumination in any size room. Includes (-09) Brushed Nickel, (-20) Antique Bronze, and (-30) white finials for use with matching Progress Lighting fans. Universal style lets you use with any indoor fan that accept an accessory light. Quick-connect wiring makes the installation process quick and easy. Includes two 3000K, 800 lumen, Title 24 certified LED bulbs.

## Specifications:

- Unfinished (-01)
- Steel construction Etched glass Bowl Elegant alabaster glass bowl casts an inviting illumination.
- Includes (-09) Brushed Nickel, (-20) Antique Bronze, and (-30) white finials for use with matching Progress Lighting fans.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Ideal for bedroom, den or kitchen lighting.
- Includes two 3000K, 800 lumen, Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016
- Mounting No for outlet box included
- 6" of wire supplied

## Performance:

Number of Modules	2
Input Power	10w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	800/80 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	25,000 (L70/TM-21)
EMI/RFI	Title 24
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	1 year warranty
Labels	UL Dry location listed

## P2612-01WB

## Images:



## Dimensions:

Diameter: 12"  
Height: 7-11/16"

Glass  
Width: 10-3/4"  
Height: 6"

# P2612 Fan Light Kit

• Dry location listed 

## Description:

Alabaster style glass bowl ceiling fan light kit casts an inviting illumination in any size room. Includes (-09) Brushed Nickel, (-20) Antique Bronze, and (-30) white finials for use with matching Progress Lighting fans. Universal style lets you use with any indoor fan that accept an accessory light. Quick-connect wiring makes the installation process quick and easy. Includes two 3000K, 800 lumen, Title 24 certified LED bulbs.

## Specifications:

- Unfinished (-01)
- Steel construction Etched glass Bowl Elegant alabaster glass bowl casts an inviting illumination.
- Includes (-09) Brushed Nickel, (-20) Antique Bronze, and (-30) white finials for use with matching Progress Lighting fans.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Ideal for bedroom, den or kitchen lighting.
- Includes two 3000K, 800 lumen, Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016
- Mounting No for outlet box included
- 6" of wire supplied

## Performance:

Number of Modules	2
Input Power	10w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	800/80 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	25,000 (L70/TM-21)
EMI/RFI	Title 24
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	1 year warranty
Labels	UL Dry location listed

## P2612-01WB

## Images:



## Dimensions:

Diameter: 12"  
Height: 7-11/16"

Glass  
Width: 10-3/4"  
Height: 6"