

# P2628 Fan Light Kit

• Dry location listed 

## Description:

Three-light fan kit with an etched glass bowl from the Trinity Collection. Finials included are -09 Brushed Nickel, -20 Antique Bronze, -30 White and -77 Forged Bronze that match a variety of Progress Lighting fans. Quick-connect wiring makes it easy to install to a fan that accept an accessory light. Gracefully exotic, the Trinity Collection offers classic sophistication for interiors. Includes three 3000K, 800 lumen, Title 24 certified LED bulbs.

## Specifications:

- Unfinished (-01)
- Steel construction Etched glass Bowl Add style and light to your ceiling fan with this universal fan light kit.
- Etched glass bowl.
- Finials included are -09 Brushed Nickel, -20 Antique Bronze, -30 White and -77 Forged Bronze.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Ideal for bedroom, den or kitchen lighting.
- Includes two 3000K, 800 lumen, Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016
- Mounting No for outlet box included
- 6" of wire supplied
- 

## Performance:

Number of Modules	2
Input Power	10w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	800/80 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	25,000 (L70/TM-21)
EMI/RFI	Title 24
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	1 year warranty
Labels	UL Dry location listed

## P2628-01WB

## Images:



## Dimensions:

Diameter: 13-3/8"

Height: 6-3/8"

Glass

Width: 13-3/8"

Height: 6-3/8"

# P2628 Fan Light Kit

• Dry location listed 

## Description:

Three-light fan kit with an etched glass bowl from the Trinity Collection. Finials included are -09 Brushed Nickel, -20 Antique Bronze, -30 White and -77 Forged Bronze that match a variety of Progress Lighting fans. Quick-connect wiring makes it easy to install to a fan that accept an accessory light. Gracefully exotic, the Trinity Collection offers classic sophistication for interiors. Includes three 3000K, 800 lumen, Title 24 certified LED bulbs.

## Specifications:

- Unfinished (-01)
- Steel construction Etched glass Bowl Add style and light to your ceiling fan with this universal fan light kit.
- Etched glass bowl.
- Finials included are -09 Brushed Nickel, -20 Antique Bronze, -30 White and -77 Forged Bronze.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Ideal for bedroom, den or kitchen lighting.
- Includes two 3000K, 800 lumen, Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016
- Mounting No for outlet box included
- 6" of wire supplied
- 

## Performance:

Number of Modules	2
Input Power	10w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	800/80 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	25,000 (L70/TM-21)
EMI/RFI	Title 24
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	1 year warranty
Labels	UL Dry location listed

## P2628-01WB

## Images:



## Dimensions:

Diameter: 13-3/8"

Height: 6-3/8"

Glass

Width: 13-3/8"

Height: 6-3/8"