

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P3925-15ET

## Dome Glass CTC

Two-light flush mount with dome shaped glass, solid trim and decorative knobs. The polished chrome finish has an etched glass shade.

- Dome shaped glass.
- Solid trim and decorative knobs.
- Etched glass shade.

**Category:** Close-to-Ceiling

**Finish:** Polished Chrome (plated)

**Construction:** Steel Construction

**Glass/Shade:** Etched glass bowl



**Diameter:** 13-1/4"

**Height:** 5-7/8"

Glass

Width: 9-13/16"

Height: 3-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted  Mounting strap for outlet box included  Ceiling pan covers a standard 4" octagonal recessed outlet box  13.1875" W., 1.375" ht., 13.1875" depth	Pre-wired  6" of wire supplied  120 V	Quantity:  Two 75w max. Medium Base  E26 base porcelain sockets	cCSAus Damp location listed  1 year warranty