



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P4010ACSC0W CO/Smoke Detector

Kidde Safety

| | |
|------------------|--|
| Catalog Number | P4010ACSC0W |
| Manufacturer | Kidde Safety |
| Description | Combination Smoke and Carbon Monoxide Alarm, Smoke and Carbon Monoxide Alarm, Battery Powered Type; Photoelectric/Electrochemical Operation Type; UL 217/2034, Nfpa 72 Approval; 85 Decibel At 10 Foot Horn Type; 120 Volt Ac 60 Hertz Voltage Rating/Source |
| Weight per unit | 0.6000 (lbs/each) |
| Product Category | Smoke & Heat Detectors |

Features

| | |
|----------------------------|-------------------------------|
| Horn Type | 85 Decibel at 10 Foot |
| LED/Strobe Type | Flashing LED |
| Number of Interconnections | 24 in |
| Operation Type | Photoelectric/Electrochemical |
| Voltage Rating/Source | 120 Volt AC 60 Hertz |

Descriptions

| | |
|------------------------|--|
| Additional Information | Overall Dimension 5.59 Inch Diameter x 1.91 Inch Depth; Battery Type 3 Volt Sealed-In Lithium; Relative Humidity Rating 10 to 95 Percent RH (Non-Condensing); Temperature Rating 40 to 100 Deg F |
| Commodity Description | SMOKE & HEAT DETECTORS |
| Description | CO/SMOKE DETECTOR |
| extra long description | SMOKE AND CARBON MONOXIDE ALARM, WIRE-FREE TYPE; PHOTOELECTRIC, ELECTROMECHANICAL OPERATION TYPE; UL APPROVAL; 85 DECIBEL AT 10 FOOT HORN TYPE; 120 VOLT AC 60 HERTZ VOLTAGE RATING/SOURCE; GREEN LED INDICATING DEVICE WORKING, AMBER LED INDICATING ERROR, RED LED INDICATING DANGER DETECTED LED/STROBE TYPE; 24 INTERCONNECTION(S); BATTERY TYPE 3 VOLT SEALED LITHIUM; TEMPERATURE RATING 40 TO 100 DEG F; HUMIDITY RATING 10 TO 95 PERCENT RH NON-CONDENSING; OVERALL DIMENSION 5.59 INCH DIAMETER X 1.19 INCH DEPTH |
| Long Description | COMBINATION SMOKE AND CARBON MONOXIDE ALARM, SMOKE AND CARBON MONOXIDE ALARM, BATTERY POWERED TYPE; PHOTOELECTRIC/ELECTROCHEMICAL OPERATION TYPE; UL 217/2034, NFPA 72 APPROVAL; 85 DECIBEL AT 10 FOOT HORN TYPE; 120 VOLT AC 60 HERTZ VOLTAGE RATING/SOURCE |
| Product Type | Combination Smoke and Carbon Monoxide Alarm |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Kidde |
| GTIN | 00047871273232 |
| Manufacturers Part Number | 21027323 |
| UPC | 047871273232 |

Taxonomies, Classifications, and Categories

| | |
|------|--|
| Type | Smoke and Carbon Monoxide Alarm, Battery Powered |
|------|--|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.6 |

Uses, Certifications, and Standards

| | |
|----------|----------------------|
| Approval | UL 217/2034, NFPA 72 |
|----------|----------------------|