

# Eaton P48G11S0312

Catalog Number: P48G11S0312

3 KVA Mini Power Center 1PH 480V-120/240V 12 spaces



## General specifications

### Product Name

Eaton Mini-Power center

### Catalog Number

P48G11S0312

### UPC

786680225529

### Product Length/Depth

8.9 in

### Product Height

29.5 in

### Product Width

11.9 in

### Product Weight

168 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

NAFTA

### Certifications

IEEE Certified  
CSA Certified  
UL Listed  
ANSI

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 3R

### Frame

284

### Insulation

180 °C

### Mounting

Wall Mount

### Tap size

2 at -5% FCBN

### Type

Mini-power center

### Wiring connection

M48G11C

## Performance Ratings

### Frequency rating

60 Hz

### kVA

3 kVA

### Kva Rating

3 kVA

### Phase

Single-phase

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Sound Level

NEMA ST-20

### Temperature rise

115 °C rise

### Volt ampere rating

3 kVA

## Miscellaneous

### Modification 1

NEMA 3R

### Weathershield

Not required

## Resources

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - P48G11S0312](#)