Specifications



Photo is representative





Eaton P48G11S03P

Eaton Mini-Power Center, Single-phase, PV: 480V, Taps: 2 at -5% FCBN, SV: 120/240V, 115°C, 3 kVA, Al windings, Frame: 283, Indoor-Outdoor.

General specifications	
PRODUCT NAME	Eaton Mini-Power center
CATALOG NUMBER	P48G11S03P
UPC	786680140136
PRODUCT LENGTH/DEPTH	8.9 in
PRODUCT HEIGHT	27.5 in
PRODUCT WIDTH	11.9 in
PRODUCT WEIGHT	130 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL Listed ANSI CSA Certified IEEE Certified



Physical Attributes	
COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	283
TAP SIZE	2 at -5% FCBN
ТҮРЕ	Mini-power center
WIRING CONNECTION	97A3K

Performance Ratings	
FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	3 kVA

Miscellaneous	
WEATHERSHIELD	Indoor-Outdoor

Resources	
CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
MULTIMEDIA	Eaton's Transformer Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - P48G11S03P

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.







