

Specifications

Photo is representative



Eaton P48G11S05P

Eaton Mini-Power Center,
Single-phase, PV: 480V,
Taps: 2 at -5% FCBN, SV:
120/240V, 115°C, 5 kVA,
Al windings , Indoor-
Outdoor.B45, Frame: 284

Physical Attributes

| | |
|--------------------------|-------------------|
| COIL MATERIAL | Aluminum |
| ENCLOSURE | NEMA 3R |
| FRAME | 284 |
| TAP SIZE | 2 at -5% FCBN |
| TYPE | Mini-power center |
| WIRING CONNECTION | 110A5K |

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Mini-Power center |
| CATALOG NUMBER | P48G11S05P |
| UPC | 786680140204 |
| PRODUCT LENGTH/DEPTH | 8.9 in |
| PRODUCT HEIGHT | 16 in |
| PRODUCT WIDTH | 11.9 in |
| PRODUCT WEIGHT | 146 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | NEMA Compliant |
| CERTIFICATIONS | UL Listed IEEE Certified CSA Certified ANSI |

Specifications

Photo is representative



Eaton P48G11S05P

Eaton Mini-Power Center,
Single-phase, PV: 480V,
Taps: 2 at -5% FCBN, SV:
120/240V, 115°C, 5 kVA,
Al windings , Indoor-
Outdoor.B45, Frame: 284

Physical Attributes

| | |
|--------------------------|-------------------|
| COIL MATERIAL | Aluminum |
| ENCLOSURE | NEMA 3R |
| FRAME | 284 |
| TAP SIZE | 2 at -5% FCBN |
| TYPE | Mini-power center |
| WIRING CONNECTION | 110A5K |

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Mini-Power center |
| CATALOG NUMBER | P48G11S05P |
| UPC | 786680140204 |
| PRODUCT LENGTH/DEPTH | 8.9 in |
| PRODUCT HEIGHT | 16 in |
| PRODUCT WIDTH | 11.9 in |
| PRODUCT WEIGHT | 146 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | NEMA Compliant |
| CERTIFICATIONS | UL Listed IEEE Certified CSA Certified ANSI |