

# Specifications



Photo is representative



## Eaton P48G11S05P

Eaton Mini-Power Center, Single-phase, PV:  
480V, Taps: 2 at -5% FCBN, SV: 120/240V,  
115°C, 5 kVA, Al windings , Indoor-  
Outdoor.B45, Frame: 284

### General specifications

<b>PRODUCT NAME</b>	Eaton Mini-Power center
<b>CATALOG NUMBER</b>	P48G11S05P
<b>UPC</b>	786680140204
<b>PRODUCT LENGTH/DEPTH</b>	8.9 in
<b>PRODUCT HEIGHT</b>	16 in
<b>PRODUCT WIDTH</b>	11.9 in
<b>PRODUCT WEIGHT</b>	146 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	NEMA Compliant
<b>CERTIFICATIONS</b>	UL Listed IEEE Certified CSA Certified ANSI



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	284
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	110A5K

## Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

## Performance Ratings

FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	5 kVA

## Resources

CATALOGS	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
MULTIMEDIA	<a href="#">Eaton's Transformer Flex Center</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - P48G11S05P</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

