

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5683-31

Welbourne

The Welbourne collection features hexagonal framework with vine inspired scrolls and clear beveled glass panels. Cast aluminum construction with durable powder coat finish. One-light wall lantern.

Category: Outdoor

Finish: Textured Black (painted)

Construction: Die-cast aluminum construction

Glass: Clear beveled glass panels



Width: 9-3/8"

Height: 16"

Depth: 11-1/4"

H/CTR: 3-1/2"

Glass: 3-3/4" Top, 2-5/16" Bottom

Height: 7-1/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Back plate covers a standard 4" hexagonal recessed outlet box</p> <p>4-1/2", 7"ht.</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p>	<p>Quantity: 1</p> <p>100W Medium Base</p> <p>Medium ceramic socket</p>	<p>UL-CUL Wet location listed</p> <p>1 year warranty</p> <p>Companion Chain hung lantern, Post top lantern, Wall lantern fixtures are available</p>



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5683-31

Welbourne

The Welbourne collection features hexagonal framework with vine inspired scrolls and clear beveled glass panels. Cast aluminum construction with durable powder coat finish. One-light wall lantern.

Category: Outdoor

Finish: Textured Black (painted)

Construction: Die-cast aluminum construction

Glass: Clear beveled glass panels



Width: 9-3/8"

Height: 16"

Depth: 11-1/4"

H/CTR: 3-1/2"

Glass: 3-3/4" Top, 2-5/16" Bottom

Height: 7-1/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" hexagonal recessed outlet box 4-1/2", 7"ht.	Pre-wired 6" of wire supplied 120V	Quantity: 1 100W Medium Base Medium ceramic socket	UL-CUL Wet location listed 1 year warranty Companion Chain hung lantern, Post top lantern, Wall lantern fixtures are available