

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P5878-31

## Onion Lantern

Detailed finials, end caps and scroll work in a durable power coat finish, featuring clear beveled glass panels and cast aluminum frames. One-light wall lantern.

- Textured Black finish.
- Clear beveled glass curved panels.
- Cast aluminum.

**Category:** Outdoor

**Finish:** Textured Black (painted)

**Construction:** Die-cast aluminum Construction, solid brass interior components

**Glass/Shade:** Clear Beveled glass curved panels



**Width:** 6-1/2"  
**Height:** 21-1/4"  
**Depth:** 10"  
**H/CTR:** 13-1/8"

**Glass**  
**Width:** 2"  
**Height:** 5"  
**Height:** 5"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting strap for outlet box included  Back plate covers a standard 4" octagonal recessed outlet box  4.5" W., 12" ht.	Pre-wired  6" of wire supplied  120 V	Quantity:  One 100w max. Medium Base  E26 base porcelain socket	UL-CUL Wet location listed  1 year warranty