



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P82222830K 7.25\"/>

Catalog Number	P82222830K
Manufacturer	Progress Lighting
Description	The P8222 Delivers A Solution For Flush Mount, For Both Residential and Commercial Markets. In Addition, The P8222 Is Wet Located, Title 24 - JA8 - 2019 and Is A Cost Effective Solution For Fire Rated Applicaiton. The P8222 Luminaire Unites Performance, Cost and Safety Benefits.
Weight per unit	1.2 (lbs/each)
Product Category	Led Surface Architectural & SP

Features

amperage rating	0.122
dimmable	Yes
Fixture Type	Flush Mount
indoor/outdoor	Indoor
Lamp Type	Solid State
Lamp Wattage	17
Light Type	LED
lumens	1231
Number of Lamps	1
Power Source	Hardwired
Voltage Rating	120
Warranty	5-Year limited
Wire Length	6

Material, Color, and Finish

Color	White
Color Rendering Index	90
color temperature	3000 k
Style	Modern, Transitional

Dimensions and Weight

Height	1.1875
Length	7.25
Width	7.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	7.25" LED 1LT RND FLSH MN TRIAC DIMMING - NO HRDWR
extra long description	PROG P8222-28-30K P8222-28-30K 7.25
Long Description	The P8222 delivers a solution for flush mount, for both residential and commercial markets. In addition, the P8222 is wet located, Title 24 - JA8 - 2019 and is a cost effective solution for fire rated applicaiton. The P8222 luminaire unites performance, cost and safety benefits.
Product Type	P8222-28-30K 7.25IN Led Flush MT T24
Short Description	One-Lgt White LED Flush Mount

Manufacturer Information

Brand	Progress Lighting
GTIN	00785247205615
Manufacturers Part Number	P8222-28-30K
UPC	785247205615

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Flush-Mount

Packaging

Carton	1
Weight	1.28
Weight Per each	1.16

Uses, Certifications, and Standards

Frequency Rating	60 Hz
------------------	-------