



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P832TG 4" Non-IC Incandescent Remodel Can

Progress Lighting

Catalog Number	P832TG
Manufacturer	Progress Lighting
Description	For Use In Existing Ceilings. Integral Flange On Housing and Exclusive Locking Bars Permits Quick Mounting On Ceilings From 1/2 In to 1 In Thick. UL and CUL Listed For Damp Locations.
Weight per unit	1.6 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Coating	unfinished
dimensions	11-3/8 W., 5-1/2 ht.
indoor/outdoor	Indoor
Lamp Type	A19
Material	Galvanized Steel
Number of Lamps	1
pallet quantity	216
Power Source	Hardwired
Socket Type	socket
Voltage Rating	120

Material, Color, and Finish

Color	Unfinished
fixture material	galvanized steel
Style	Utilitarian/Commodity

Dimensions and Weight

Height	5.5
Length	11.375
Width	4.8125

Descriptions

Description	4" NON-IC INCADESCENT REMODEL CAN
extra long description	PROG P832-TG P832-TG 4in NON-IC REM
Long Description	For use in existing ceilings. Integral flange on housing and exclusive locking bars permits quick mounting on ceilings from 1/2 in to 1 in thick. UL and CUL listed for damp locations.
Product Type	P832-TG 4IN Non-IC Remodel Can



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PROGRESS
GTIN	00785247104970
Manufacturers Part Number	P8367-WL28
UPC	785247104970

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	4in Remodel Housing

Trade Size

aperture size	4
---------------	---

Packaging

Carton	1
Package	6
Weight Per each	1.6

Uses, Certifications, and Standards

Mounting	CEILING
standard	UL-CUL