

Specifications

Photo is representative



Eaton PDG22G0020TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Two Pole, 20A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X2T100)

General specifications

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG22G0020TFFL
UPC	786679945636
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	3.75 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CSA CCC Marked IEC 60947-2

Delivery program

AMPERAGE RATING	20 A
CIRCUIT BREAKER FRAME TYPE	Complete breaker
FRAME	2
NUMBER OF POLES	Two-pole

Technical data - Electrical

VOLTAGE RATING	600 Vac
-----------------------	---------

General information

CIRCUIT BREAKER TYPE	PD2 Global
CLASS	Class A
TRIP TYPE	T298

Technical data - Mechanical - Terminals

TERMINALS	Standard Terminals Load Only
------------------	------------------------------

Technical information

INTERRUPT RATING	35 kAIC at 480 Vac
INTERRUPT RATING RANGE	65 kAIC @240V (UL) 55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC) 8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC) 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC) 30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC) 18 kAIC @600V (UL/CSA) 36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC) 10 kAIC Icu @250 Vdc 20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC) 10 kAIC Icu @125 Vdc 35 kAIC @480V (UL)

Resources

3D CAD DRAWING PACKAGE	Eaton Power Defense PDG22G0020TFFL 3D drawing
APPLICATION NOTES	Consulting application guide - molded case circuit breakers Power Defense brochure Power Defense molded case circuit breaker selection poster
BROCHURES	Power Defense technical selling booklet Power Defense molded case circuit breakers - Frame 2 product aid
CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2 PDG4 CB report Power Defense Declaration concerning California's Proposition 65 PDG4 CCC certification PDG2 CB report EU Declaration of Conformity - Power Defense molded case circuit breakers
INSTALLATION INSTRUCTIONS	Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA Handle Attachment Instructions (IL012260EN).pdf Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA225RF instructions - IL012245EN H01 Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring instructions - IL012316EN Power Defense Frame 2 box terminal (steel), 100A, 2 pole instructions - IL012234EN H02 Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2256W instructions - IL012242EN H01 Power Defense Frame 2 tunnel terminal (aluminum), 150A, 2 pole instructions - IL012238EN H02 Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA150RF instructions - IL012244EN H01

[Power Defense Frame 2 tunnel terminal \(aluminum\), 100A, 2 pole instructions - IL012237EN H02](#)

[Power Defense Frame 2 PDG2 and PDC\(E\)9 breaker instructions - IL012106EN](#)

[Power Defense Frame 2 screw terminal end cap kit, 225A, 2 pole instructions - IL012257EN H01](#)

[Power Defense Frame 2 multi wire connector kit - PDG2X3\(2\)\(4\)TA2253W instructions - IL012243EN H01](#)

[Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 50A, 2 pole instructions - IL012236EN H02](#)

[Power Defense Frame 2 clamp terminal \(steel\), 20A, 2 pole instructions - IL012246EN H02](#)

[Power Defense Frame 2 global terminal shield, 2 pole - IL012330EN](#)

[Power Defense Frame 2 locking devices and handle block instructions - IL012149EN](#)

[Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions-IL012239EN H01](#)

[Power Defense Frame 2 global interphase barrier 2 pole - IL012324EN](#)

INSTALLATION VIDEOS

[Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated Instructions.rh](#)

[Power Defense Frame 2 withTMTU, Shunt Trip UVR Animated Instructions.rh](#)

MULTIMEDIA

[Power Defense Frame 6 Trip Unit How-To Video](#)

[Power Defense molded case circuit breakers](#)

[Eaton Power Defense for superior arc flash safety](#)

[Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

	Power Defense Breakers Power Defense Frame 5 Trip Unit How-To Video Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PDG22G0020TFFL
TIME/CURRENT CURVES	Power Defense time current curve Frame 2 - PD2
	Molded case and low-voltage power circuit breaker health Intelligent circuit protection yields space savings Single and double break MCCB performance revisited Making a better machine Molded case and low-voltage breaker health Safer by design: arc energy reduction techniques
WHITE PAPERS	

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

