



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PDT110 110 Punchdown Tool W/110 Blade For CAT6 Jack *Panduit Corporation*

|                  |   |
|------------------|---|
| Catalog Number   | PDT110                                    |
| Manufacturer     | Panduit Corporation                       |
| Description      | Punchdown Tool, 110 Style Idcs, Utp Cable |
| Weight per unit  | 0.3150 (lbs/each)                         |
| Product Category | Tools & Testers                           |

### Features

|             |    |
|-------------|----|
| Cable Entry | NA |
|-------------|----|

### Dimensions and Weight

|       |      |
|-------|------|
| Width | 1.44 |
|-------|------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 110 PUNCHDOWN TOOL W/110 BLADE FOR CAT6 JACK |
| extra long description | PAN PDT110 110 Punchdown Termination Tool    |
| Long Description       | Punchdown Tool, 110 Style IDCs, UTP Cable    |
| Product Type           | 110 Punchdown Termination Tool               |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | PANDUIT        |
| GTIN                      | 00074983390205 |
| Manufacturers Part Number | PDT110         |
| Model                     | NA             |
| UPC                       | 074983390205   |

### Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | HAND TOOLS                 |
| Type                 | Single Pair Punchdown Tool |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Weight Per each | 0.315 |

### Uses, Certifications, and Standards

|                          |                                  |
|--------------------------|----------------------------------|
| Application              | NA                               |
| environmental conditions | NA                               |
| standard                 | RoHS directive is not applicable |