

Commercial Specification Grade Thermoplastic Wallplates

Mid-Size



INDUSTRIAL
COMMERCIAL
RESIDENTIAL

0-16
WALLPLATES

TESTING & CODE COMPLIANCE

- UL and cUL Listed, UL File #E33216
- Meets current Federal Specifications as tested to UL 514
- Meets all CSA requirements, C22.2 no. 42.1, CSA file #9294 (4413-02).

MATERIAL CHARACTERISTICS




Meets flammability requirements per UL 94, V2 rated.
Temperature Rating: -40°C to 70°C.

Commercial Thermoplastic Wallplates

FEATURES


- Mid-Size wallplates are 0.375" (9.53mm) longer and wider on all sides than standard to cover large wallboard openings.
- Assures NEC®-required gap coverage for most wallboard-to-box openings.
- Virtually unbreakable polycarbonate construction - high structural rigidity, long-term form retention.
- Screw-Catch™ feature holds plate mounting screw captive for ease of installation.
- Superior abrasion and impact resistance.
- Color-matched mounting screws captive in 1 and 2 gang plates for faster installation - helps eliminate lost screws on the job.

Toggle Switch	
1 Gang	
Color	Catalog No.
Almond	PJ1A
Brown	PJ1B
Black	PJ1BK
Gray	PJ1GY
Red	PJ1RD
Ivory	PJ1V
Light Almond	PJ1LA
White	PJ1W
2 Gang	
Color	Catalog No.
Almond	PJ2A
Brown	PJ2B
Black	PJ2BK
Gray	PJ2GY
Red	PJ2RD
Ivory	PJ2V
Light Almond	PJ2LA
White	PJ2W
3 Gang	
Color	Catalog No.
Almond	PJ3A
Brown	PJ3B
Black	PJ3BK
Gray	PJ3GY
Ivory	PJ3V
Light Almond	PJ3LA
White	PJ3W



Commercial Specification Grade Thermoplastic Wallplates

Mid-Size



INDUSTRIAL
COMMERCIAL
RESIDENTIAL

0-16
WALLPLATES

TESTING & CODE COMPLIANCE

- UL and cUL Listed, UL File #E33216
- Meets current Federal Specifications as tested to UL 514
- Meets all CSA requirements, C22.2 no. 42.1, CSA file #9294 (4413-02).

MATERIAL CHARACTERISTICS

Meets flammability requirements per UL 94, V2 rated.
Temperature Rating: -40°C to 70°C.

Commercial Thermoplastic Wallplates

FEATURES

- Mid-Size wallplates are 0.375" (9.53mm) longer and wider on all sides than standard to cover large wallboard openings.
- Assures NEC®-required gap coverage for most wallboard-to-box openings.
- Virtually unbreakable polycarbonate construction – high structural rigidity, long-term form retention.
- Screw-Catch™ feature holds plate mounting screw captive for ease of installation.
- Superior abrasion and impact resistance.
- Color-matched mounting screws captive in 1 and 2 gang plates for faster installation – helps eliminate lost screws on the job.

Toggle Switch


1 Gang

Color	Catalog No.
Almond	PJ1A
Brown	PJ1B
Black	PJ1BK
Gray	PJ1GY
Red	PJ1RD
Ivory	PJ1V
Light Almond	PJ1LA
White	PJ1W



2 Gang

Color	Catalog No.
Almond	PJ2A
Brown	PJ2B
Black	PJ2BK
Gray	PJ2GY
Red	PJ2RD
Ivory	PJ2V
Light Almond	PJ2LA
White	PJ2W



3 Gang

Color	Catalog No.
Almond	PJ3A
Brown	PJ3B
Black	PJ3BK
Gray	PJ3GY
Ivory	PJ3V
Light Almond	PJ3LA
White	PJ3W

