

Specifications



Photo is representative

Eaton PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V, Three-phase, 4W, 600A, 42 circuit, Copper bus

General specifications

PRODUCT NAME	Eaton Pow-R-Stock PRL2A panelboard
CATALOG NUMBER	PRL2A3600X42CL
UPC	786687011125
PRODUCT LENGTH/DEPTH	85 in
PRODUCT HEIGHT	7 in
PRODUCT WIDTH	18 in
PRODUCT WEIGHT	75 lb
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL 67

Product specifications

TYPE	PRL2A Panelboard
AMPERAGE RATING	600A
BUS MATERIAL	Copper
BUS RATING	600 A
FEED TYPE	Top/bottom
NUMBER OF CIRCUITS	42
NUMBER OF POLES	Single-pole, three-pole
OPERATING TEMPERATURE	40°C
PHASE	Three-phase
SHORT-CIRCUIT RATING	35 A
WIRE SIZE	#4 AWG-350 kcmil
CIRCUIT BREAKER RATING	NEMA
CURRENT - MAX	600 A
NEMA RATING	NEMA 1, NEMA 3R
SERIES	PRL2a
VOLTAGE - MAX	480 V

Resources

MULTIMEDIA

[Pow-R-Line Xpert family overview](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - PRL2A3600X42CL](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

