



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS30AC1I 30A 120/277VAC B+S Wire SP SW Iv

Pass & Seymour/Legrand

Catalog Number	PS30AC1I
Manufacturer	Pass & Seymour/Legrand
Description	1-Pole Toggle Switch, Back and Side-Wire, 30A 120/277V
Weight per unit	0.2021 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	SP
actuator	Toggle
amperage rating	30
Contact Rating	30Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	False
Load Rating	30 A @ 120/277 VAC
Load Type	Universal, Fluorescent, Incandescent, LED, Halogen, CFL, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	30A 120/277VAC B+S WIRE SP SW IV
extra long description	P&S PS30AC1I 30A 120/277VAC B+S WIR
Features	Chemical Resistant
Long Description	1-Pole Toggle Switch, Back and Side-Wire, 30A 120/277V
Product Type	30A 120/277VAC B+S Wire SP SW I
Special Features	Heavy duty switch, back & side wire, with lock



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195538
Manufacturers Part Number	PS30AC1-I
UPC	785007195538

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2021

Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting standard	WALL CULUS, UL20, FEDSPEC