



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS30SSAX 30A 600VAC N/F Safety Switch W/Aux.

Pass & Seymour/Legrand

Catalog Number	PS30SSAX
Manufacturer	Pass & Seymour/Legrand
Description	Non-Fusible Safety Switch With Auxiliary Contact, 30 Amps, 600 Vac. The First Non-Metallic Nema 4X Non-Fusible Safety Switch Line UI Listed As Suitable As Motor Disconnect Per Nec Article 430.109(A)(6). Pass and Seymour Non-Fusible Safety Switches Feature Extra-Tough Components, Including An Impact-Resistant Valox Nema 4X Enclosure. and An Innovative Design That Delivers Safe, Sure Operation Under The Worst Conditions.
Weight per unit	2.3 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

action	Motor Disconnect Switch
amperage rating	30
connection	Hard Wired
Contact Configuration	1 N.O. & 1 N.C.
Contact Rating	10A @ 600VAC
insulation	Complies with NEMA 4X
Material	Valox 357®
operating cycles	Electrical: 10,000 Cycles;Mechanical: 15,000 Cycles
Poles	4-Way
Switch Type	Switch Handle
Voltage	600.0 V
Voltage Rating	600

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Height	9.69
Width	4.88



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	30A 600VAC N/F SAFETY SWITCH W/AUX.
extra long description	P&S PS30SSAX 30A 600VAC N/F SAFETY
Long Description	Non-Fusible Safety Switch with Auxiliary Contact, 30 Amps, 600 VAC. The first non-metallic NEMA 4X Non-Fusible Safety Switch line UL Listed as Suitable as Motor Disconnect per NEC Article 430.109(A)(6). Pass and Seymour Non-Fusible Safety Switches feature extra-tough components, including an impact-resistant Valox NEMA 4X enclosure. And an innovative design that delivers safe, sure operation under the worst conditions.
Product Type	30A 600VAC N/F Safety Switch W/Aux.
Special Features	Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage. Nonconductive, watertight, corrosion-, heat-, and impact-resistant Valox® enclosure ensures NEMA 4X and 12 ratings and withstands the harshest industrial environments. Corrosion-resistant, stainless steel captive screws speeds installation, minimize risk of lost parts, and withstand abuse. Adjustable mounting feet can be moved to center of unit for instant strut- or pole-mounting with

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007150032
Manufacturers Part Number	PS30SSAX
UPC	785007150032

Taxonomies, Classifications, and Categories

Category Description	Rotary Disconnects
Type	Non-Fusible Safety Switch with Auxiliary Contact

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Weight Per each	2.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Industrial
Enclosure	IP67 Suitability:NEMA Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt)
environmental conditions	Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability: Flammability: UL94 5VA and VO Classification: UV Resistance: All enclosure materials are UV stable
Frequency Rating	60.0 Hz
Mounting	External adjustable feet with five (5) positions. Can be mounted directly to channel or strut (no washers required).
standard	CULUS, UL, CSA