



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS5969Y Straight Blade Conn 3W 15A 125V YI

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | PS5969Y |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Connector 2-Pole 3-Wire 15A 125a |
| Weight per unit | 0.1476 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|----------------|
| amperage rating | 15 |
| connection | Wire Grounding |
| Material | Nylon |
| Number of Wires | 3.0 |
| Poles | 2 |
| Voltage Rating | 125 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Yellow |
|-------|--------|

Dimensions and Weight

| | |
|------|---------|
| Size | 1.83 in |
|------|---------|

Descriptions

| | |
|------------------------|--|
| Description | STRAIGHT BLADE CONN 3W 15A 125V YL |
| extra long description | P&S PS5969Y STR BLD CONN 3W 15A 125 |
| Long Description | Straight Blade Connector 2-Pole 3-Wire 15A 125A |
| Product Type | STR BLD Conn 3W 15A 125V Y |
| Special Features | Self hinge, enclosed terminals and molded finger grips |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007237511 |
| Manufacturers Part Number | PS5969-Y |
| UPC | 785007237511 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | Residential cord connectors |
| Type | Straight Blade |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.1476 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| nema rating | 5-15R |
| standard | CULUS, UL 498 |