



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS60SSAX 60A 600VAC N/F Safety Switch W/Aux

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | PS60SSAX |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Non-Fusible Safety Switch With Auxiliary Contact, 60 Amps, 600 Vac. The First Non-Metallic Nema 4X Non-Fusible Safety Switch Line UI Listed As Suitable As Motor Disconnect Per Nec Article 430.109(A)(6). Pass and Seymour Non-Fusible Safety Switches Feature Extra-Tough Components, Including An Impact-Resistant Valox Nema 4X Enclosure. and An Innovative Design That Delivers Safe, Sure Operation Under The Worst Conditions. |
| Weight per unit | 4.4 (lbs/each) |
| Product Category | Non-Fusible Disconnect Safety |

Features

| | |
|-----------------------|---|
| action | Motor Disconnect Switch |
| amperage rating | 60 |
| connection | Hard Wired |
| Contact Configuration | 1 N.O. & 1 N.C. |
| Contact Rating | 10A @ 600VAC |
| insulation | Complies with NEMA 4X |
| Material | Valox 357® |
| operating cycles | Electrical: 10,000 Cycles;Mechanical: 15,000 Cycles |
| Poles | 4-Way |
| Switch Type | Switch Handle |
| Voltage | 600.0 V |
| Voltage Rating | 600 |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Color | Gray |
| Finish | Matte |

Dimensions and Weight

| | |
|--------|-------|
| Height | 12.38 |
| Width | 6.31 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 60A 600VAC N/F SAFETY SWITCH W/AUX |
| extra long description | P&S PS60SSAX 60A 600VAC N/F SAFETY |
| Long Description | Non-Fusible Safety Switch with Auxilliary Contact, 60 Amps, 600 VAC. The first non-metallic NEMA 4X Non-Fusible Safety Switch line UL Listed as Suitable as Motor Disconnect per NEC Article 430.109(A)(6). Pass and Seymour Non-Fusible Safety Switches feature extra-tough components, including an impact-resistant Valox NEMA 4X enclosure. And an innovative design that delivers safe, sure operation under the worst conditions. |
| Product Type | 60A 600VAC N/F Safety Switch W/Aux. |
| Special Features | Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage. Nonconductive, watertight, corrosion-, heat-, and impact-resistant Valox® enclosure ensures NEMA 4X and 12 ratings and withstands the harshest industrial environments. Corrosion-resistant, stainless steel captive screws speeds installation, minimize risk of lost parts, and withstand abuse. Adjustable mounting feet can be moved to center of unit for instant strut- or pole-mounting with |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007150131 |
| Manufacturers Part Number | PS60-SSAX |
| UPC | 785007150131 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Residential GFCI devices |
| Type | Safety Switch |

Trade Size

| | |
|----------|------|
| Amperage | 60.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 4.35 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Industrial |
| Enclosure | IP67 Suitability:NEMA Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt) |
| environmental conditions | Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability: Flammability: UL94 5VA and VO Classification: UV Resistance: All enclosure materials are UV stable |
| Frequency Rating | 60.0 Hz |
| Mounting | External adjustable feet with five (5) positions. Can be mounted directly to channel or strut (no washers required). |
| standard | CULUS, UL, CSA |