

Eaton PSG240E

Catalog Number: PSG240E

Power Supply, 240W, Single-phase, 100-240V input voltage, 24 Vdc \pm 2% output voltage, 2.9A input current, 10A output current, 47-63 Hz, 85-264V, 120-375 Vdc, Aluminum enclosure, Heavy-duty screw terminals

General specifications



Photo is representative

Product Name

Eaton PSL low-profile power supply

UPC

786685215464

Product Height

4.67 in

Product Weight

2.63 lb

Catalog Number

PSG240E

Product Length/Depth

4.76 in

Product Width

3.35 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

RoHS Compliant
German Safety
CE Marked

Certifications

CSA Certified
cULus/UL 60950-1
UL 508
EN Listed
IEC Rated
cUL Certified

Catalog Notes

Ratings for single-phase are at 115V. 0 Hz at DC input.

Product specifications

Special features

Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection, finger-safe cover

Operating temperature - max

75 °C

Operating temperature - min

-20 °C

Power consumption

240 W

Phase

Single-phase

Voltage rating

85-264 Vac, 100-375 Vdc

Frequency rating

47-63 Hz

Enclosure material

Aluminum

Output voltage

24 V

Terminals

Heavy-duty screw

Input voltage

100-240 Vac

Series

PSG

Rated operational current

2.9 A input

15 A surge

10 A output

Resources

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - PSG240E](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)