

# Eaton PSG60E24RM

Catalog Number: PSG60E24RM

Eaton PSG general purpose power supply, 60W, Single-phase, 24 Vdc output voltage, Metal enclosure, Removable terminals

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton PSG general purpose power supply	PSG60E24RM

**UPC**  
786685520971

<b>Product Length/Depth</b>	<b>Product Height</b>
6.2 in	2.1 in

<b>Product Width</b>	<b>Product Weight</b>
6.5 in	0.37 lb

<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	German Safety RoHS Compliant

**Certifications**  
CSA Certified  
EN Listed  
cUL Certified  
IEC Rated  
UL 508  
cULus/UL 60950-1

## Product specifications

### Special features

Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection

### Operating temperature - max

75 °C

### Operating temperature - min

-20 °C

### Power consumption

60 W

### Phase

Single-phase

### Enclosure material

Metal

### Output voltage

24 V

### Terminals

Removable

### Series

PSG

## Resources

### Brochures

[Eaton's PSG Series Power Supplies](#)

### Installation instructions

[Installation Instructions for PSG60E Power Supply](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - PSG60E24RM](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)