

---

## 15 AMP NEMA L715 CONNECTOR - BLACK BACK, WHITE FRONT BODY

PSL715C | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Turnlok Connector 3wire 15amp 277v



- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow, White  
Type: Connector  
Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes

UN SPSC: 39121403

## DIMENSIONS

Diameter (US): 1.516"

Length (US): 2.598"

## TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: L715

Volts: 277V

Volts (AC): 277

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



---

## 15 AMP NEMA L715 CONNECTOR - BLACK BACK, WHITE FRONT BODY

PSL715C | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Turnlok Connector 3wire 15amp 277v



- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow, White  
Type: Connector  
Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes

UN SPSC: 39121403

## DIMENSIONS

Diameter (US): 1.516"

Length (US): 2.598"

## TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: L715

Volts: 277V

Volts (AC): 277

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

