

MINITERMS

Male & Female Plugs & Adapters, Plier Taps & Pin Terminal

PM, PF, PTC, PT Series

SPECIFICATIONS

- **Nylon Male Plugs:** Electro tin plated copper, Nylon, 600V, 75 °C.
- **Nylon Female Plugs:** Electro tin plated copper, Nylon, 600V, 105 °C.
- **Vinyl Piercing Taps:** Electro tin plated copper, Vinyl (PVC), 600V, 75 °C.
- **Vinyl Pin Terminal:** Electro tin plated copper, 600V, 75 °C.
- **Un-Insulated Male/Female Adapters:** Brass, quick disconnect easy-entry, 600V, 105 °C.

FEATURES

- Uninsulated/Nylon Female Plugs are styled with safety and reliability.
- Vinyl Plier Taps have an insulated piercing tap.
- Vinyl Pin Terminals are designed for use in terminal blocks.
- Un-Insulated Male/Female adapters have similar tongue to a quick disconnects for use in terminal blocks or interconnect splices.




FIG. NO.	STYLE	INSULATION TYPE	WIRE RANGE	STUD SIZE	RATINGS	LENGTH (L) (IN.)	WIDTH (W) (IN.)	SEAM TYPE	"S" PACKS		PRO PACKS		STD PACKS		BULK PACKS	
									CAT. NO.	QTY	CAT. NO.	QTY	CAT. NO.	QTY	CAT. NO.	QTY
1	Plugs Male	Un-insulated	22-18	0.157	—	0.630	0.145	Butted	—	—	—	—	PM22-157	100	PM22-157-BULK	1000
1	Plugs Male	Un-insulated	16-14	0.157	—	0.630	0.136	Butted	—	—	—	—	PM16-157	100	PM16-157-BULK	1000
2	Plugs Male	Nylon	22-18	0.157	UR	0.890	0.145	Butted	—	—	—	—	PM22-157N	100	PM22-157N-BULK	1000
2	Plugs Male	Nylon	16-14	0.157	UR	0.890	0.145	Butted	—	—	—	—	PM16-157N	100	PM16-157N-BULK	1000
3	Plugs Female	Un-insulated	22-18	0.157	—	0.680	0.194	Butted	—	—	—	—	PF22-157	100	PF22-157-BULK	1000
3	Plugs Female	Un-insulated	16-14	0.157	—	0.680	0.185	Butted	—	—	—	—	PF16-157	100	PF16-157-BULK	1000
4	Plugs Female	Nylon	22-18	0.157	UR	1.000	0.128	Butted	—	—	—	—	PF22-157N	100	PF22-157N-BULK	1000
4	Plugs Female	Nylon	22-18	0.157	—	1.234	0.309	Butted	—	—	—	—	PFS22-157N	100	PFS22-157N-BULK	1000
4	Plugs Female	Nylon	16-14	0.157	UR	1.000	0.150	Butted	—	—	—	—	PF16-157N	100	PF16-157N-BULK	1000
4	Plugs Female	Nylon	16-14	0.157	—	1.233	0.339	Butted	—	—	—	—	PFS16-157N	100	PFS16-157N-BULK	1000
4	Plugs Female	Nylon	16-14	0.197	—	1.233	0.339	Butted	—	—	—	—	PFS16-197N	100	PFS16-197N-BULK	1000
5	Plier Tap Connector	Vinyl	22-18	n/a	cULus	0.790	0.550	—	—	—	—	—	PTC22-18	100	PTC22-18-BULK	500
5	Plier Tap Connector	Vinyl	16-14	n/a	cULus	0.790	0.550	—	—	—	—	—	PTC16-14	100	PTC16-14-BULK	500
5	Plier Tap Connector	Vinyl	12-10	n/a	cULus	0.800	0.740	—	—	—	—	—	PTC12-10	50	PTC12-10-BULK	250
6	Pin Terminal	Vinyl	22-18	n/a	cULus	0.930	0.078	Butted	—	—	—	—	PT-22V	100	PT-22V-BULK	1000
6	Pin Terminal	Vinyl	16-14	n/a	cULus	0.930	0.078	Butted	—	—	—	—	PT-16V	100	PT-16V-BULK	1000
6	Pin Terminal	Vinyl	12-10	n/a	cULus	1.120	0.107	Butted	—	—	—	—	PT-12V	50	PT-12V-BULK	500
7	Male/Female Adapter	Un-insulated	n/a	0.250	—	0.825	0.564	—	DMT250-3-S	15	DMT250-3-P	60	DMT250-3	100	DMT250-3-BULK	1000
8	Male/Female Adapter 90	Un-insulated	n/a	0.250	—	0.825	0.564	—	—	—	—	—	250-3-Z	100	250-3-Z-BULK	1000