



PLUGTAIL® THREE-WAY 20 AMP TOGGLE SWITCH, LIGHT ALMOND

PT20AC3LA | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Three-Way Toggle Switch, 20amp 120/277vac, Light Almond

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.
- Impact- and chemical- resistant cover.
- Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.
- One-piece nickel-plated mounting strap for superior corrosion resistance.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Auto-ground clip assures positive ground.
- Shallow design for easier installation.
- Heavy-duty bumpers for quiet, smooth operation.
- No exposed terminals create a finger-safe application before, during, and after installation.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Product Series: PlugTail
Type: Toggle
Number Of Poles: 3-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 111
CSA Standard: Yes
cULus: Yes
Federal Spec: Yes
UL Standard: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.073"
Height (US): 3.281"
Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 20A
Volts: 120/277VAC
Volts (AC): 120/277
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

