



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PTRA6STRB25 90 Degree 25" PT Conn Strand

Pass & Seymour/LeGrand

| | |
|------------------|--|
| Catalog Number | PTRA6STRB25 |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Connector, 2 Poles, Gray, 25 In Length, -40 °C Operating Temperature, +60 °C Operating Temperature |
| Weight per unit | 0.0700 (lbs/each) |
| Product Category | Outlets, Jacks, & Plates |

Features

| | |
|---------------------|--|
| Dielectric Strength | Withstands 2000V minimum |
| media | Yes |
| Number of Wires | 3 |
| Poles | Double Pole |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 12 |

Dimensions and Weight

| | |
|------|-----|
| Size | 7.5 |
|------|-----|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 90 DEGREE 25" PT CONN STRAND |
| extra long description | P&S PTR A6STRB25 90 DEGREE 25 IN PT |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007044577 |
| UPC | 785007044577 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Residential cord connectors |
| Type | PlugTail™ Connector - Right Angle |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 25 |
| Weight Per each | 0.07 |

Uses, Certifications, and Standards

| | |
|--------------------------|-----------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | Device, Wall |
| standard | CULUS, cULus UL498 |