



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV146LFM 18-14AWG #6STD Blue Vny Insld Fork TRML

Panduit Corporation

| | |
|------------------|---|
| Catalog Number | PV146LFM |
| Manufacturer | Panduit Corporation |
| Description | Locking Fork Terminal, Vinyl Insulated, Funnel Entry, 18- 14 Awg, #6 Stud Size, Bulk Package. |
| Weight per unit | 0.0023 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------------|
| connection | Funnel Entry |
| insulation | Vinyl |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | #14 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Blue |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|----|
| Size | #6 |
|------|----|

Descriptions

| | |
|------------------------|---|
| Description | 18-14AWG #6STD BLUE VNY INSLTD FORK TRML |
| extra long description | PAN PV14-6LF-M Pan-Term® PV14-6LF-M |
| Long Description | Locking Fork Terminal, vinyl insulated, funnel entry, 18- 14 AWG, #6 stud size, bulk package. |
| Product Type | Pan-Term® PV14-6LF-M Fork Terminal, Blue, Vinyl, 14-18 Awg, |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983808076 |
| Manufacturers Part Number | PV14-6LF-M |
| UPC | 074983808076 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Ring Terminal |

Availability

| | |
|-------------|------|
| minimum qty | 1000 |
|-------------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1000 |
| Weight Per each | 0.0023 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Enclosure | Fork shape |
| Mounting | 5/16 |
| standard | CSA Certified LR31212;UL Listed 587H E52164 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |