



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV146LFWM Fork Term Bulk-PK *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | PV146LFWM |
| Manufacturer | Panduit Corporation |
| Description | Locking Fork Terminal, Vinyl Insulated, Funnel Entry, 18- 14 Awg, #6 Stud Size, Wide Tongue, Bulk Package. |
| Weight per unit | 2.6 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------------|
| connection | Funnel Entry |
| insulation | Vinyl |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | #14 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Blue |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|----|
| Size | #6 |
|------|----|

Descriptions

| | |
|------------------------|--|
| Description | FORK TERM BULK-PK |
| extra long description | PAN PV14-6LFW-M Pan-Term® PV14-6LFW |
| Long Description | Locking Fork Terminal, vinyl insulated, funnel entry, 18- 14 AWG, #6 stud size, wide tongue, bulk package. |
| Product Type | Pan-Term® PV14-6LFW-M Loose Piece Terminal |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983809493 |
| Manufacturers Part Number | PV14-6LFW-M |
| UPC | 074983809493 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Ring Terminal |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1000 |
| Weight Per each | 2.6 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Enclosure | Fork shape |
| Mounting | 5/16 |
| standard | UL Listed 587H E52164; CSA Certified LR31212 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |