



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV4 Encl NM12 Vertical PB Encl

*Cooper B-Line/Cable Tray*

Catalog Number	PV4
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Push Button Enclosures, 7.25" Height, 4.75" Length, 6.25" Width, Nema 12, Screw Cover, PV Enclosure, Surface Mounted, Medium Single Door, External Mounting Feet, Carbon Steel, Oil-Resistant Gasket
Weight per unit	4.0 (lbs/each)
Product Category	Control Station Enclosures

### Features

dimensions	4.7500 IN X 6.2500 IN X 7.2500 IN
Material	Carbon Steel
Number of Holes	4

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	3.25 In Width X 2.75 In Depth X 10.25 In Height
------	---

### Descriptions

Description	ENCL NM12 VERTICAL PB ENCL
extra long description	B-LINE PV4 TYPE 12 VRTL PUSHBUTTON
Features	Eaton's B-Line series push button enclosures provide reliable environmental protection and are designed to mount standard 30.5 mm or miniature 22.5 mm oil-tight pushbuttons, pilot lights and switches
Long Description	Eaton B-Line series push button enclosures, 7.25" height, 4.75" length, 6.25" width, NEMA 12, Screw cover, PV enclosure, Surface mounted, Medium single door, External mounting feet, Carbon steel, Oil-resistant gasket
Product Type	Type 12 VRTL Pushbutton Enc
Special Features	Device Hole Size 30.5 mm

### Manufacturer Information

Brand	Eaton
GTIN	00782051702460
UPC	782051702460

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Push button enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	3.97

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	Wall, Feet
nema rating	12
standard	UL 508A,NEMA,CSA C22.2.