

Specifications



Photo is representative

Eaton PVML-7-UNV1

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 127 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 61W

Certifications and compliances

AREA CLASSIFICATION	Ordinary, Hazardous Locations
STANDARDS TYPE	NEC/CEC, IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-7-UNV1
UPC	662276862050
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb

Specifications



Photo is representative

Eaton PVML-7-UNV1

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 127 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 61W

Certifications and compliances

AREA CLASSIFICATION	Ordinary, Hazardous Locations
STANDARDS TYPE	NEC/CEC, IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-7-UNV1
UPC	662276862050
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb