



A.



B.



C.



D.

PX50, PX100, PX300, & PX600 Series Safety Transformers



- Supply 12 volts to pool/spa lights, submersible fixtures, and outdoor garden lights
- Mounting brackets on the top and bottom

3R Beige Steel Enclosure

	Model #	Input Voltage	Output Voltage	Watts
A.	PX50	120 VAC, ½ Amp	12 or 13 VAC	50
	PX100	120 VAC, 1 Amp	12 or 13 VAC	100
	PX300	120 VAC, 3 Amp	12, 13, or 14 VAC	300
B.	PX600	120 VAC, 6 Amp	12, 13, or 14 VAC	600

3R Stainless Steel Enclosure

	Model #	Input Voltage	Output Voltage	Watts
C.	PX50S	120 VAC, ½ Amp	12 or 13 VAC	50
	PX100S	120 VAC, 1 Amp	12 or 13 VAC	100
	PX300S	120 VAC, 3 Amp	12, 13, or 14 VAC	300
D.	PX600S	120 VAC, 6 Amp	12, 13, or 14 VAC	600

Rating:

PX50/S, PX100/S, PX300/S

Size: 7 ¼" (18.4 cm) H x 5 ¼" (13.3 cm) W x 4 ½" (11.4 cm) D

Knockouts:

Bottom: (4) combination ½" – ¾"

Left: (2) combination ½" – ¾"

Back: (2) combination ½" – ¾"

Right: (2) combination ½" – ¾"

PX600/S

Size: 10" (25.4 cm) H x 10" (25.4 cm) W x 5" (12.7 cm) D

Knockouts:

Bottom: (2) combination ½" – ¾", (4) combination ¾" – 1"

Left: (2) combination ½" – ¾"

Back: (2) combination ½" – ¾"

Right: (2) combination ½" – ¾"