



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QB1015EP Bolt On 1P 15A Equip Protect Gfci BRKR

Eaton Corp

Catalog Number	QB1015EP
Manufacturer	Eaton Corp
Description	Eaton QB Gfci Circuit Breaker, Bolt-On Equipment Protection, 15A, 10 Kaic, Single-Pole, 120/240V, Non-Interchangeable, 30 Ma Trip Sensitivity, Bolt-On, #14-4 Awg, QB
Weight per unit	0.4800 (lbs/each)
Product Category	20240605104318

Features

connection	BOLT-ON
dimensions	4.0000 IN X 3.5000 IN X 1.0000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	BOLT ON 1P 15A EQUIP PROTECT GFCI BRKR
extra long description	ETN QB1015EP BOLT-ON GFEP, 30MA, 1
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB GFCI circuit breaker,Bolt-on equipment protection,15A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,30 mA Trip sensitivity,Bolt-on,#14-4 AWG,QB
Product Type	Bolt-On Gfep, 30MA, 1 Pole, 10KAIC, 15a

Manufacturer Information

Brand	Eaton Corp
Manufacturers Part Number	QB1015EP

Taxonomies, Classifications, and Categories

Type	GFCI circuit breakers
------	-----------------------

Packaging

Carton	1
Weight Per each	0.48



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -
OtherOtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper Converged

standard

UL 489