

Specifications

Eaton QBGFEP2030

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,30A,10 kAIC,Two-pole,120/240V,Non-Interchangeable,QBGF



General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2030
UPC	786679145173
PRODUCT LENGTH/DEPTH	5.6 in
PRODUCT HEIGHT	0.7 in
PRODUCT WIDTH	2.4 in
PRODUCT WEIGHT	0.7 lb
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Resources

**SPECIFICATIONS AND
DATASHEETS**

[Eaton Specification Sheet -
QBGFEF2030](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
[Eaton.com](#)

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

