

# Eaton QBGFEP2040

Catalog Number: QBGFEP2040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 40A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, QBGF

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QBGFEP2040
<b>UPC</b>	<b>Product Length/Depth</b>
786679145180	6.125 in
<b>Product Height</b>	<b>Product Width</b>
2.25 in	3.5 in
<b>Product Weight</b>	<b>Certifications</b>
0.85 lb	UL 943
<b>Catalog Notes</b>	
HACR rated	

## Physical Attributes

### Circuit breaker type

QBGF

### Number of poles

Two-pole

### Type

Ground fault circuit breaker

## Performance Ratings

### Amperage Rating

40 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Special features

Bolt-on mounting

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBGFEP2040](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)